



BE163T

### Earth leakage add-on-block 3P 63A 100mA A Class 1mod

#### Technical properties

##### Voltage

Rated operational voltage $U_e$	240 - 415 V
Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	4000 V

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Electric current

Rated residual operating current $I_{dn}$	100 mA
Rated current	63 A

##### Architecture

Number of poles	3
Neutral position	Right

##### Capacity

Number of modules	1
-------------------	---

##### Connectivity

Type of connection	Screw terminal
--------------------	----------------

##### Dimensions

Height	121 mm
Width	70,80 mm
Depth	69,10 mm