



DNG5002507030B

**Slotted panel trunking made of PVC DNG 50x25mm stone grey**

**Technical properties**

**Architecture**

Flexible	No
----------	----

**Configuration**

Side wall configuration	Slotted
-------------------------	---------

**Electric current**

Current leak stable	Yes
---------------------	-----

**Dimensions**

Trunking height	50 mm
Length	2000 mm
Trunking width	25 mm
Slot width	5 mm
Tongue width	7.5 mm

**Cover, door**

Lid shape	loose
-----------	-------

**Materials**

Colour	stone grey
Material	PVC
Material group	plastic
Type of surface treatment	untreated

**Installation, mounting**

Base punching	DIN 43659
---------------	-----------

**Cable**

Number of wires 1,5 mm <sup>2</sup> - 40% filling degree	43
Internal/useful cross section	918 mm <sup>2</sup>
Number of wires 2,5 mm <sup>2</sup> - 40% filling degree	31
Number of wires 1,0 mm <sup>2</sup> - 40% filling degree	60

**Standards**

European directive RoHs	voluntary compliance
UL 94 classification	V0

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Fireproof classification	M1