



EC12160CT

Current Transformer with RJ45 output BGUK 3-Phase 160A/330mV Class 1 pitch 25mm

Technical properties

Functions

Accuracy class	1
----------------	---

Dimensions

Height	80 mm
Width	76 mm
Depth	76 mm
Height of opening	15 mm
Width of opening	30 mm

Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Rated insulation voltage U_i	3000 V
--------------------------------	--------

Use conditions

Operating temperature	-25 - 50 °C
Storage/transport temperature	-40 - 85 °C

Electric current

Max. intensity of primary	160 A
---------------------------	-------

Installation, mounting

Mounting on	Busbar, Cable
-------------	---------------