



EC25250CT

Current Transformer with RJ45 output BGUK 3-Phase 250A/330mV Class 1 pitch 35mm

Technical properties

Specific identification attributes for Protection

Filter Type product	3-phase current transformer replacement
---------------------	---

Functions

Accuracy class	1
----------------	---

Dimensions

Height	80 mm
Width	105 mm
Depth	54 mm
Height of opening	25 mm
Width of opening	21 mm

Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Voltage

Rated insulation voltage Ui	3000 V
-----------------------------	--------

Use conditions

Operating temperature	-25 - 50 °C
Storage/transport temperature	-40 - 85 °C

Electric current

Max. intensity of primary	250 A
---------------------------	-------

Installation, mounting

Mounting on	Busbar, Cable
-------------	---------------