



EC40630CT

**Current Transformer with RJ45 output BGUK 3-Phase 630A/330mV Class 1 pitch 45mm**

**Technical properties**

**Specific identification attributes for Protection**

Filter Type product	3-phase current transformer replacement
---------------------	---

**Functions**

Accuracy class	1
----------------	---

**Dimensions**

Height	90 mm
Width	140 mm
Depth	54 mm
Height of opening	31 mm
Width of opening	31 mm

**Connectivity**

Type of connection	Plug-in connection
--------------------	--------------------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Voltage**

Rated insulation voltage Ui	3000 V
-----------------------------	--------

**Use conditions**

Operating temperature	-25 - 50 °C
Storage/transport temperature	-40 - 85 °C

**Electric current**

Max. intensity of primary	630 A
---------------------------	-------

**Installation, mounting**

Mounting on	Busbar, Cable
-------------	---------------