



EE860



## Motion detector comfort 220°, IP55, wall mounted, blanc

### Technical properties

#### Detection

Detection angle	220 - 220
Type of sensor	Movement detector

#### Settings

Time delay	5 S - 30 Min
------------	--------------

#### Lighting

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Dimensions

Width	91 mm
Recommended installation height	2,50 - 2,50 m

#### Use conditions

Operating temperature	-20 - 55 °C
-----------------------	-------------

#### Materials

Colour	White
Material	Plastic

#### Safety

Ingress Protection (IP) class	IP55
-------------------------------	------

#### Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

#### Texts

Function	Presence simulation, Can be used as a single unit, main device or extension unit
Installation mode	For wall and ceiling mounting, corner installation with adapter
Type of connection	With screw terminals