



EE860



**IP55**



## Motion detector comfort 220°, IP55, wall mounted, blanc

### Technical properties

#### Architecture

Fixing mode	surface-mounting
-------------	------------------

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Dimensions

Height of installed product	2.5 m
Recommended installation height	2.5 m

#### Power supply

Supply voltage	230 V +10% / -15%
----------------	-------------------

#### Detection

Detection angle	220 °
Detection angle	220 °
Frontal detecting distance	16 m
Side detecting distance	10 m

#### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

#### Lighting control

Response brightness, adjustable	≈ 5...1000 lx
Brightness measurement range	5 / 1000 Lux

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

#### Settings

Response value sensitivity adjustable	Yes
Delay time, adjustable	5 s...30 mn

#### Scope of delivery

Component	with fitting material
-----------	-----------------------

#### Equipment

Remote controllable	EE806
Angle of horizontal detection	220 °

Slewing	vertically slewing and horizontally rotating
---------	--

**Safety**

Protection index IP	IP55
REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-20...55 °C
Storage/transport temperature	-20...60 °C

**Identification**

Application, usage	Motion detector
Main design line	Motion detectors