



EEN003

**IP55**

## Cell for twilight switch, wall mounted

### Technical properties

#### Dimensions

Depth of installed product	41.3 mm
Height of installed product	32 mm
Length	131.4 mm
Width of installed product	48 mm

#### Length

Maximum connection distance between receiver and transmitter	100m
--	------

#### Lighting control

Brightness measurement range	5 / 2000 Lux
------------------------------	--------------

#### Installation, mounting

Mounting type	surface-mounted
---------------	-----------------

#### Connection

Conductor cross-section	0.75...4 mm <sup>2</sup>
-------------------------	--------------------------

#### Cable

Wire	Cable length between twilight switch and brightness sensor max. 100 m
------	---

#### Settings

Delay ON	60 s
Delay OFF	80 s

#### Equipment

Probe type	light sensor
------------	--------------

#### Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

#### Use conditions

Operating temperature	-25...70 °C
Storage/transport temperature	-25...70 °C

#### Identification

Main design line	House electronics
------------------	-------------------