



EER518

Motion detector highbay 360° surface mounted NO contact detection height 8m

Technical properties

Detection

| | |
|-----------------|-------------------|
| Detection angle | 360 - 360 ° |
| Type of sensor | Movement detector |

Settings

| | |
|------------|-------------|
| Time delay | 1 Min - 1 h |
|------------|-------------|

Lighting

| | |
|--------------------------------|------------|
| Response brightness adjustable | 5- 2000 lx |
|--------------------------------|------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Dimensions

| | |
|---------------------------------|---------|
| Built-in depth | 78 mm |
| Recommended installation height | 6 - 9 m |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Materials

| | |
|----------|---------|
| Material | Plastic |
|----------|---------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP41 |
|-------------------------------|------|

Installation, mounting

| | |
|----------------------------|------------------|
| Mounting on | Surface mounting |
| Suitable for outdoor usage | No |