



EGK103

Digital time switch 1 Channel weekly cycle + Bluetooth key

Technical properties

Functions

With GPS	No
hour program	Yes

Main electrical features

Rated operational voltage Ue	230 V
Nominal voltage	230 V
Type of supply voltage	AC
Frequency	50/60 Hz

Electric current

Switching current at 250 V~	16 A
-----------------------------	------

Frequency

Frequency range	50...60 Hz
-----------------	------------

Power

Power consumed	0.55 VA
Power consumption (operation)	350 mW

Measurement

Running accuracy	± 1.5 s/day
------------------	-------------

Battery

Battery / storage battery	with battery type: Lithium 1/2 AA
---------------------------	-----------------------------------

Fluorescent bulbs control

Fluorescent lamps	max. 1000 VA
Max. power fluo. duo lamp comp. series	1000 W
Compact fluorescent lamps	400 W
Fluorescent lamps parallel compensated	400 W

Incandescent bulbs control

230 V incandescent lamps and halogen lamps	2300 W
--	--------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Number of contacts	1
Type of connection	with screw terminal

Contact	with failsafe break contact (NC contact)
Type of connection	with screw
Settings	
Number of program steps	56
Shortest switching time	1 mn
Programming cycle	1X7D.
Programming	Programming possible without mains voltage
Annual program	No
Astro program	No
Daily program	Yes
Time	with automatic summer/winter time change-over
Weekly program	Yes
Scope of delivery	
Memory card included	No
Equipment	
Type of programmable thermostat	Digital
Number of switching times for on/off	56
Supply failure reserve	5 years
Summer-/winter switchover	Yes
With cyclic program	No
With holidays program	No
With Impulse program	Yes
With preset programm	No
With random program	No
Use	
Local operation/hand operation	Yes
Safety	
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Working accuracy	$\pm 1,5 \text{ s} / 24\text{H}$
Relative humidity	95 %
Identification	
Device family	EG