



ESC240

**Contactor 40A, 2NO, 230V~50Hz**

**Technical properties**

**Architecture**

Type of order	Not applicable
Number of poles	2 P

**Configuration**

Number of modules	3
-------------------	---

**Main electrical features**

Rated operational voltage Ue	400 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	440 V
DC control voltage	0 V
Command voltage AC	230 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated current	40 A
Thermal rated current outside of housings	40 A
Acceptable current load with AC7 category A	40 A
Acceptable current load with AC7 category B	25 A

**Dimensions**

Depth of installed product	60 mm
Height of installed product	85 mm
Width of installed product	54 mm

**Power**

Inrush power absorbed	62.5 VA
Operating consumption	5.7 VA
Total power loss under IN	7.9 W
Power loss per contact	3.2 W
Power dissipation per coil	1.5 W
Contact rating with 230 V in AC7 category A	7.3 kW
Contact rating with 230 V in AC7 category B	2.6 kW
Contact rating with 400 V in AC7 category A	22 kW
Contact rating with 400 V in AC7 category B	7.8 kW

<b>Tripping</b>	
Time of response when opening	20 ms
Time of response when closing	25 ms
<b>Resistance</b>	
Winding resistance	770 Ω
<b>Endurance</b>	
Electric endurance in number of cycles	30000
Number of mechanical operations	100000
<b>Fluorescent bulbs control</b>	
Max. power with fluorescent parallel lamps	1300 VA
Fluorescent lamps in duo circuit	3000 VA
Max. load fluorescent lamp	1900 VA
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	4000 W
<b>Installation, mounting</b>	
Tightening torque	Coil: 2,5Nm ; Power: 3,5Nm
<b>Connection</b>	
Connection cross-sect. flexible conductor	1,5 / 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 25mm <sup>2</sup>
Number of contacts	2
Type of contacts	2NO
Type of connection	with screw
Connection cross-section of the control cable solid	1 / 2.5 mm <sup>2</sup>
<b>Equipment</b>	
Can be accessorized	Yes
<b>Use</b>	
Local operation/hand operation	No
<b>Safety</b>	
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C