



EV100



## Remote control dimmer universal 1000W

### Technical properties

#### Voltage

Rated operational voltage  $U_e$  230 - 230 V

#### Frequency

Frequency 50 - 50 Hz

#### Materials

Colour Grey

RAL code 7035

#### Dimensions

Height 85 mm

Width 88,50 mm

Depth 65 mm

#### Power

Power consumption during operation 15 VA

Power consumption standby 3 W

Power incandescent lamp 20 - 1000 W

#### Use conditions

Operating temperature -10 - 45 °C

#### Connection

Cross-section rigid conductor 1.5 - 10 mm<sup>2</sup>

Cross-section flexible conductor 1 - 16 mm<sup>2</sup>

#### Capacity

Number of modules 5

#### Texts

Dimming principle Automatic load detection

Installation mode For mounting on DIN rail

Junction Connection for illuminated (max. 5 mA) or standard push-buttons

Type of connection With screw terminals