



EZD100



## ON Delay time relay 24-240V AC/DC

### Technical properties

#### Frequency

Frequency 50 - 60 Hz

#### Use conditions

Operating temperature -25 - 55 °C

#### Connection

Cross-section flexible conductor 0.5 - 2.5 mm<sup>2</sup>

Cross-section rigid conductor 0.5 - 2.5 mm<sup>2</sup>

#### Capacity

Number of modules 1

#### Dimensions

Height 87 mm

Width 17,50 mm

Depth 65 mm