



EZM100



Multifunction time relay 12-240V AC/DC

Technical properties

Frequency

Frequency 50 - 60 Hz

Use conditions

Operating temperature -25 - 55 °C

Connection

Cross-section flexible conductor 0.5 - 2.5 mm²

Cross-section rigid conductor 0.5 - 2.5 mm²

Capacity

Number of modules 1

Dimensions

Height 87 mm

Width 17,50 mm

Depth 65 mm