



FD72DN

Enclosure, NewVegaD, 1200x550x193mm, 168 modules, surface-mounted, distribution

Technical properties

Configuration

Module	with terminals
Number of modules	168

Main electrical features

Nominal voltage	230/400 V
-----------------	-----------

Electric current

Rated current	160 A
---------------	-------

Dimensions

Depth of installed product	193 mm
Internal depth	189 mm
Height of installed product	1200 mm
Width of installed product	550 mm
Width in division units	24
Thickness of sidewall material	2 mm

Cover, door

Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	none / closed
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	4
--------------------------	---

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	7
Quantity of rails	7
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	No

Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No