



FU42DN

Enclosure, NewVegaD, 837x550x150mm, 96 modules, flush-mounted, distribution

Technical properties

Connection

Number of conduit inlets 4

Installation, mounting

Suitable for outdoor usage No

Mounting on Flush mounting

Electric current

Rated current 160 A

Equipment

Number of rails 4

Number of rows 4

Number of section in width 2

With lock No

Has neutral terminal block No

Has earthing terminal block No

Has mounting plate No

Capacity

Number of modules 96

Dimensions

Height 837 mm

Width 600 mm

Depth 150 mm

Built-in width 550 mm

Built-in depth 110 mm

Number of width units 24

Cover, door

Door/cover is transparent No

Materials

Material Metal, Plastic

RAL code 9010

Colour Pure white

Safety

Protection class Isolation class II

Impact resistance IK IK07

Subject to technical modifications

