



FU52DN

Enclosure, NewVegaD, 987x550x150mm, 120 modules, flush-mounted, distribution

Technical properties

Architecture

Fixing mode flush-mounting

Configuration

Module with terminals

Number of modules 120

Electric current

Rated current 160 A

Dimensions

Insertion depth 110 mm

Depth of installed product 150 mm

Internal depth 110 mm

Height of installed product 987 mm

Installation height 987 mm

Width of installed product 600 mm

Width in division units 24

Thickness of sidewall material 1 mm

Built-in width 550 mm

Cover, door

Cover type With Notch

Door locking without

Door leave single

Cover type none / closed

Transparent cover or door No

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material Plastic/metal

Installation, mounting

Suitable for outdoor use No

Connection

Number of conduit inlets 4

Settings

Enclosure type Distributor empty cabinet

Equipment

Number of rows	5
Quantity of section in width	2
Quantity of rails	5
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	No

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No