



FU62DN

Enclosure, NewVegaD, 1137x550x150mm, 144 modules, flush-mounted, distribution

Technical properties

Connection

Number of conduit inlets	4
--------------------------	---

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

Electric current

Rated current	160 A
---------------	-------

Equipment

Number of rails	6
Number of rows	6
Number of section in width	2
With lock	No
Has neutral terminal block	No
Has earthing terminal block	No
Has mounting plate	No

Capacity

Number of modules	144
-------------------	-----

Dimensions

Height	1137 mm
Width	600 mm
Depth	150 mm
Built-in width	550 mm
Built-in depth	110 mm
Number of width units	24

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Metal, Plastic
RAL code	9010
Colour	Pure white

Safety

Protection class	Isolation class II
Impact resistance IK	IK07

Subject to technical modifications

Ingress Protection (IP) class	IP30
Locking type	Without lock