



FU72DN

**Enclosure, NewVegaD, 1287x550x150mm, 168 modules, flush-mounted, distribution**

**Technical properties**

**Connection**

Number of conduit inlets 4

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Flush mounting

**Electric current**

Rated current 160 A

**Equipment**

Number of rails 7

Number of rows 7

Number of section in width 2

With lock No

Has neutral terminal block No

Has earthing terminal block No

Has mounting plate No

**Capacity**

Number of modules 168

**Dimensions**

Height 1287 mm

Width 600 mm

Depth 150 mm

Built-in width 550 mm

Built-in depth 110 mm

Number of width units 24

**Cover, door**

Door/cover is transparent No

**Materials**

Material Metal, Plastic

RAL code 9010

Colour Pure white

**Safety**

Protection class Isolation class II

Impact resistance IK IK07

