



GD102T

Mini-enclosure, GD, 2 module wide, protect. class IP30, without door

Technical properties

Configuration

Number of modules	2
-------------------	---

Main electrical features

Nominal voltage	230 V
-----------------	-------

Electric current

Rated current	32 A
---------------	------

Dimensions

Depth of installed product	82 mm
Internal depth	82 mm
Height of installed product	160 mm
Width of installed product	55 mm
Width in division units	2

Cover, door

Type of door closing	non keylock
Cover type	With Notch
Door locking	without
Cover type	with notch
Transparent cover or door	No

Materials

Colour	white
Colour	white

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
Quantity of rails	1
Can be accessorized	No
Earthing terminal block	No
Neutral terminal block	No

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	05
Protection class	isol.class II
Halogen free	No