



GD10T

Surface mounting enclosure

Technical properties

Connection

Number of conduit inlets	0
--------------------------	---

Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Equipment

Number of rails	1
Number of rows	1
Has neutral terminal block	Yes
Has earthing terminal block	No
Has mounting plate	No

Capacity

Number of modules	10
-------------------	----

Dimensions

Height	140 mm
Width	250 mm
Depth	65 mm
Built-in depth	65 mm
Number of width units	10

Cover, door

Number of locks	0
Door/cover is transparent	No

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Polystyrene (PS)
RAL code	9010
Colour	Pure white

Safety

Protection class	Isolation class II
------------------	--------------------

