



HA308

Load break switch 3P 200A

Technical properties

Electric current

Rated current 200 A

Connection

Cross-section rigid conductor 95 mm²

Voltage

Rated insulation voltage U_i 800 V

Rated impulse withstand voltage U_{imp} 8000 V

Power

Power loss per pole at I_n 5,80 W

Total power loss under I_n 17,40 W

Rated operational power under 400 V AC
 AC1 131000 W

Equipment

Motor drive optional No

Use conditions

Operating temperature -20 - 70 °C

Cover, door

Interlockable Yes

Safety

Ingress Protection (IP) class IP00

Architecture

Type of pole 3P

Control/operation element Long thumb grip