




HA408



**Load break switch with visible breaking 4P 200A**

**Technical properties**

**Electric current**

Rated current 200 A

**Connection**

Cross-section rigid conductor 95 mm<sup>2</sup>

**Voltage**

Rated insulation voltage  $U_i$  800 V

Rated impulse withstand voltage  $U_{imp}$  8000 V

**Power**

Power loss per pole at  $I_n$  5,80 W

Total power loss under  $I_n$  17,40 W

Rated operational power under 400 V AC  
 AC1 131000 W

**Equipment**

Motor drive optional No

**Use conditions**

Operating temperature -20 - 70 °C

**Cover, door**

Interlockable Yes

**Safety**

Ingress Protection (IP) class IP00

**Architecture**

Type of pole 4P

Control/operation element Short thumb grip