



HIC410A

Motorized changeover switch 4P 100A 400V

Technical properties

Architecture

Type of order	Not applicable
Number of poles	4 P
Type of pole	4 P
Type of case	Fixed built-in

Functions

Reversing switch	Yes
------------------	-----

Controls and indicators

Motor drive integrated	Yes
------------------------	-----

Main electrical features

Rated operational voltage Ue	380 / 415 V
Frequency	50/60 Hz

Electric current

Rated current	100 A
Short-circuit current with gI-gG fuses	50 kA
Rated short-time withstand current 1s	4 kA
Rated operational current in AC23 category A	100 A

Power

Total power loss under IN	9 W
Power loss per pole at In	3 W
Contact rating with 400 V in AC1	65 kW

Cover, door

Interlockable	Yes
---------------	-----

Installation, mounting

Tightening torque	4 - 4.4 Nm
-------------------	------------

Connection

Type of connection	with screw
--------------------	------------

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Number of auxiliary contacts as change-over contact	0
---	---

Motor drive optional	No
----------------------	----

Standards

Standard text	IEC 60947-3 ; IEC 60947-6
---------------	---------------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----