



HIC463G

Automatic transfer switch 4x 630A

Technical properties

Voltage

Rated operational voltage U _e	380 - 415 V
--	-------------

Electric current

Rated current	630 A
---------------	-------

Rated conditional short-circuit current I _{cc} with gI-gG fuses	50 kA
---	-------

Power

Rated operational power under 400 V AC AC1	414000 W
---	----------

Architecture

Number of poles	4
-----------------	---

Device construction type	Fixed built-in
--------------------------	----------------

Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----

Suitable for distribution board	Yes
---------------------------------	-----