



HTC310H

COMMUNICATION Module without inputs and outputs

Technical properties

Architecture

Fixing mode DIN rail type O (symmetrical)

Configuration

Number of modules 2

Voltage

Operating voltage 24 V DC

Standards

European directive RoHS voluntary compliance

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature -25...70 °C

Storage/transport temperature -35...70 °C