



HTC310H

COMMUNICATION Module without inputs and outputs

Technical properties

Configuration

Number of modules	2
-------------------	---

Main electrical features

Type of supply voltage	DC
------------------------	----

Voltage

Operating voltage	24 V DC
-------------------	---------

Standards

European directive RoHs	compliant
-------------------------	-----------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-25...70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Storage/transport temperature	-35...70 °C