



HTC320H

COMMUNICATION Module with inputs and outputs

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Main electrical features

| | |
|------------------------|----|
| Type of supply voltage | DC |
|------------------------|----|

Voltage

| | |
|-------------------|--------------|
| Input voltage | 24 V DC |
| Operating voltage | 24 V DC |
| Output voltage | 24...48 V DC |

Electric current

| | |
|----------------|------------|
| Input current | max. 15 mA |
| Output current | max. 50 mA |

Equipment

| | |
|--------------------------|---|
| Number of digital inputs | 2 |
|--------------------------|---|

Standards

| | |
|-------------------------|-----------|
| European directive RoHS | compliant |
|-------------------------|-----------|

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -25...70 °C |
| Storage/transport temperature | -35...70 °C |