



HTD210H

### Display for Energy MCCB

#### Technical properties

##### Main electrical features

Type of supply voltage	DC
------------------------	----

##### Voltage

Rated operational voltage in DC	24 V
---------------------------------	------

##### Dimensions

Cut-out (W x H)	92 mm
-----------------	-------

##### Power

Power absorbed	2 W
----------------	-----

##### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

##### Use conditions

Operating temperature	-10...55 °C
-----------------------	-------------

Storage/transport temperature	-10...55 °C
-------------------------------	-------------