



HXA027H

## Alarm contact NO-NC right side (x630/P630)

### Technical properties

#### Electric current

Rated current	3 A
Rated current 230 V AC15	3 A

#### Connectivity

Type of connection	quickconnect
Mounting type	Click mounting

#### Connection

Type of contacts	1x changeover
Cross-section flexible conductor	0.5 - 1.25 mm <sup>2</sup>
Cross-section rigid conductor	0.5 - 1.25 mm <sup>2</sup>

#### Voltage

Rated impulse withstand voltage Uimp	1500 V
Type voltage supply	AC/DC

#### Power

Total power loss under IN	3 W
---------------------------	-----

#### Equipment

Number of INV contacts	1
Number of NC contacts	0

#### Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------