



HXA028H

**Alarm contact-Low level NO-NC right side (x630/P630)**

**Technical properties**

**Architecture**

Fixing mode	Clipped
-------------	---------

**Main electrical features**

Rated operational voltage Ue	125 V
Type of supply voltage	AC/DC

**Voltage**

Rated impulse withstand voltage	1500 V
Rated operational voltage in DC	30 V

**Electric current**

Rated current	0.1 A
---------------	-------

**Power**

Total power loss under IN	3 W
---------------------------	-----

**Connection**

Type of contacts	1 changeover
Type of connection	quick connect

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	1
Number of auxiliary contacts as fault signal	2

**Standards**

European directive RoHS	voluntary compliance
-------------------------	----------------------