



HXC040H

Motor operator h250 24V DC

Technical properties

Architecture

Type of order motor drive

Main electrical features

Rated operational voltage U_e 0 V

Type of supply voltage DC

Voltage

DC control voltage 24 V

Command voltage AC 0 V

Rated operational voltage in DC 24 V

Power

Total power loss under I_N 24 W

Standards

European directive RoHS voluntary compliance

European directive WEEE concerned

Safety

Protection index IP IP4X

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m