



HXT042H

Motor Operator P250 230-240VAC with Auto-Reset

Technical properties

Architecture

Type of order motor drive

Main electrical features

Type of supply voltage AC

Voltage

DC control voltage 0 V

Command voltage AC 230 / 240 V

Electric current

Inrush current OFF-RESET 230-240V AC - 6A

Inrush current ON 230-240V AC - 6A

Operating current OFF-RESET 230-240V AC - 3.4A

Operating current ON 230-240V AC - 3.4A

Frequency

Frequency 50 to 60 Hz

Standards

European directive RoHS compliant

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Altitude 2000 m