



HYA006H

**Collar terminal x160 Al 4P**

**Technical properties**

**Architecture**

Number of poles 4 P

**Electric current**

Rated current 160 A

**Installation, mounting**

Tightening torque 10Nm

**Connection**

Connection cross-sect. flexible conductor 35 / 70mm<sup>2</sup>

Connection cross-sect. rigid cable 35 / 70 mm<sup>2</sup>

Conductor cross-section 35...70 mm<sup>2</sup>

**Cable**

Cable Material Cu / Al

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Degree of pollution according to IEC 60664 /  
IEC 60947-2 3

Altitude 2000 m