



HYB002H

Collar terminal x250 Al/Cu 4P

Technical properties

Architecture

Number of poles 4 P

Electric current

Rated current 250 A

Installation, mounting

Tightening torque 25Nm

Connection

Connection cross-sect. flexible conductor 35 / 150mm²

Connection cross-sect. rigid cable 35 / 185mm²

Conductor cross-section 35...185 mm²

Cable

Cable Material Cu / Al

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Degree of pollution according to IEC 60664 /
IEC 60947-2 3

Altitude 2000 m