



HYW014H

**Spread terminal extension x630/P630 3P (up to 630A)**

**Technical properties**

**Architecture**

Number of poles	3 P
Type of pole	3 P

**Electric current**

Rated current	630 A
---------------	-------

**Power**

Total power loss under IN	19 W
Power loss per pole at In	6.35 W

**Installation, mounting**

Tightening torque	18Nm
-------------------	------

**Standards**

European directive RoHS	voluntary compliance
-------------------------	----------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes