



HZI811

Controller

Technical properties

Architecture

Fixing mode Din-Rail

Configuration

Number of modules 6

Main electrical features

Frequency 50/60 Hz

Dimensions

Depth of installed product 58 mm

Height of installed product 93 mm

Width of installed product 106 mm

Power

Power consumed 7.5 VA

Measurement

Frequency measuring range 50 to 60 Hz

Voltage measurement range 110 to 400 V

Equipment

Type of display LCD

Standards

European directive WEEE concerned

Safety

Protection index IP IP2X

Use conditions

Operating temperature -20...60 °C

Altitude 2000 m

Storage/transport temperature -20...60 °C