



JG463IN

IP66 63A 3P SW NEUTRAL ISOLATOR

Technical properties

Architecture

Number of poles	4
Type of pole	3P+N

Electric current

Rated current	63 A
Acceptable current rating AC21	63 A
Acceptable current rating AC21 category A	63 A
Rated short-time withstand current I _{cw} IEC 60947	0,75 kA
Acceptable current rating AC22 category A	63 A
Acceptable current rating AC23 category A	63 A

Voltage

Rated operational voltage U _e	380 - 440 V
Rated insulation voltage U _i	440 V

Installation, mounting

Nominal tightening torque	2,50 - 2,50 Nm
---------------------------	----------------

Dimensions

Height	170 mm
Width	84 mm
Depth	87 mm

Power

Rated operational power under 400 V AC AC23	31200 W
---	---------

Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

Use conditions

Operating temperature	-5 - 40 °C
-----------------------	------------

Connection

Cross-section rigid conductor	10 - 16 mm ²
-------------------------------	-------------------------

Frequency

Frequency	50 - 60 Hz
-----------	------------