



JPD4W78S25DX

Technical properties

Architecture

Number of poles of the main switch	3
------------------------------------	---

Functions

Overvoltage protection	No
------------------------	----

Configuration

Number of modules	36
-------------------	----

Main electrical features

Frequency	50/60 Hz
-----------	----------

Electric current

Rated current	250 A
---------------	-------

Dimensions

Insertion depth	200 mm
Depth of installed product	200 mm
Internal depth	198 mm
Height of installed product	1600 mm
Width of installed product	600 mm
Thickness of sidewall material	1.2 mm

Cover, door

Type of door closing	3-point lever
Interlockable	No
Transparent cover or door	No

Connection

Number of accessible phases	78
-----------------------------	----

Equipment

Quantity of rails	3
Can be accessorized	No
With bell transformer	No
Extension possible	Yes

Safety

IK protection code against mechanical impacts	05
Protection class	isol.class I
REACH conform	No