



JPE3W60NSSDX

Technical properties

Configuration

Number of modules	36
-------------------	----

Compatibility

Suitable for lightning protection	Yes
-----------------------------------	-----

Dimensions

Insertion depth	250 mm
Depth of installed product	250 mm
Internal depth	248 mm
Height of installed product	1400 mm
Width of installed product	600 mm
Thickness of sidewall material	1.2 mm

Cover, door

Material thickness cover	1.5 mm
Type of door closing	3-point lever
Interlockable	No
Door locking	with key
Transparent cover or door	No

Materials

Copper weight of the product	2.9 kg
Material quality	Steel

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	0
--------------------------	---

Equipment

Quantity of rails	3
Extension possible	Yes

Standards

Approvals	AS/NZS 61439-3
-----------	----------------

Safety

IK protection code against mechanical impacts	IK05
Protection class	isol.class I

REACH conform

No

RoHS conform

Yes