



JPE3W60S25DW

## Technical properties

### Architecture

|                                    |                  |
|------------------------------------|------------------|
| Fixing mode                        | surface-mounting |
| Number of poles of the main switch | 3                |

### Functions

|                        |    |
|------------------------|----|
| Overvoltage protection | No |
|------------------------|----|

### Configuration

|                   |    |
|-------------------|----|
| Number of modules | 36 |
|-------------------|----|

### Main electrical features

|           |          |
|-----------|----------|
| Frequency | 50/60 Hz |
|-----------|----------|

### Electric current

|               |       |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

### Dimensions

|                                |         |
|--------------------------------|---------|
| Insertion depth                | 250 mm  |
| Depth of installed product     | 250 mm  |
| Internal depth                 | 248 mm  |
| Height of installed product    | 1400 mm |
| Width of installed product     | 600 mm  |
| Thickness of sidewall material | 1.2 mm  |

### Cover, door

|                           |    |
|---------------------------|----|
| Interlockable             | No |
| Transparent cover or door | No |

### Materials

|            |                       |
|------------|-----------------------|
| Colour     | light grey            |
| RAL colour | RAL 7035 - Light grey |
| Material   | Steel                 |

### Connection

|                             |    |
|-----------------------------|----|
| Number of accessible phases | 60 |
|-----------------------------|----|

### Equipment

|                       |     |
|-----------------------|-----|
| Quantity of rails     | 3   |
| Can be accessorized   | No  |
| With bell transformer | No  |
| Extension possible    | Yes |

**Safety**

|   |              |
|---|--------------|
| IK protection code against mechanical impacts | 05           |
| Protection index IP                           | IP66         |
| Protection class                              | isol.class I |
| REACH conform                                 | No           |
| RoHS conform                                  | Yes          |