



KB163N

## Insulated busbar 1P 63A prong 10mm<sup>2</sup> blue 13M

### Technical properties

#### Architecture

Number of poles	1 P
Type of pole	1 P

#### Configuration

Number of modules	13
-------------------	----

#### Compatibility

Intended for the compatible references	Modular devices
--	-----------------

#### Main electrical features

Rated operational voltage Ue	415 V
------------------------------	-------

#### Voltage

Max operating voltage	230 V
Rated impulse withstand voltage	4 kV

#### Electric current

Rated current	63 A
---------------	------

#### Dimensions

Length	228 mm
Pitch	17.8 mm
Fixation distance in module steps	1

#### Power supply

Number of phases for the power supply	1 phase
---------------------------------------	---------

#### Installation, mounting

Suitable to a device with an auxiliary	No
--	----

#### Connection

Suitable for product with neutral busbar	No
--	----

#### Equipment

Number of appliances to build in	13
----------------------------------	----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform

Yes

Use conditions

Insulated

Yes