



KB181A1

**Insulated prong busbar 1P 80A 16mm<sup>2</sup> 6C for RCBO**

**Technical properties**

**Architecture**

Number of poles 1 P

**Configuration**

Number of modules 11

**Voltage**

Rated impulse withstand voltage 4 kV

**Electric current**

Rated current 80 A

**Dimensions**

Length 184 mm

Pitch 17.8 mm

**Power**

Total power loss under IN 0.8 W

**Power supply**

Number of phases for the power supply 1 phase

**Installation, mounting**

Suitable to a device with an auxiliary No

**Connection**

Connection cross-sect. rigid cable 16mm<sup>2</sup>

Suitable for product with neutral busbar No

Connector type busbar prong

**Equipment**

Number of connections 6 C

Number of appliances to build in 11

**Standards**

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

**Use conditions**

