



KB181A1

Insulated prong busbar 1P 80A 16mm² 6C for RCBO

Technical properties

Architecture

Number of poles 1 P

Configuration

Number of modules 11

Voltage

Rated impulse withstand voltage 4 kV

Electric current

Rated current 80 A

Dimensions

Length 184 mm

Pitch 17.8 mm

Power

Total power loss under IN 0.8 W

Power supply

Number of phases for the power supply 1 phase

Installation, mounting

Suitable to a device with an auxiliary No

Connection

Connection cross-sect. rigid cable 16mm²

Suitable for product with neutral busbar No

Connector type busbar prong

Equipment

Number of connections 6 C

Number of appliances to build in 11

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

