



KB181A1

## Insulated prong busbar 1P 80A 16mm<sup>2</sup> 6C for RCBO

### Technical properties

#### Electric current

Rated current 80 A

#### Architecture

Number of poles 1

#### Dimensions

Length 184 mm

#### Voltage

Rated impulse withstand voltage Uimp 4000 V

#### Connection

Cross-section rigid conductor 16 mm<sup>2</sup>

Connector/plug type Phase busbar with pin

#### Capacity

Number of modules 11