



KB181G1

Insulated prong busbar 1P 80A 16mm² 9C for RCBO

Technical properties

Architecture

Number of poles	1 P
-----------------	-----

Configuration

Number of modules	13
-------------------	----

Voltage

Rated impulse withstand voltage	4 kV
---------------------------------	------

Electric current

Rated current	80 A
---------------	------

Dimensions

Length	228 mm
Pitch	17.8 mm

Power

Total power loss under IN	1.2 W
---------------------------	-------

Power supply

Number of phases for the power supply	1 phase
---------------------------------------	---------

Materials

Colour	brown
--------	-------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Connection cross-sect. rigid cable	16mm ²
Suitable for product with neutral busbar	No
Connector type	busbar prong

Equipment

Number of connections	9 C
Number of appliances to build in	13

Standards

European directive RoHS	voluntary compliance
European directive WEEE	not concerned

Safety

REACH conform	Yes
RoHS conform	Yes
Use conditions	
Insulated	Yes