



**Insulated busbar 1P 100A fork 20mm<sup>2</sup> 57M**

**Technical properties**

**Architecture**

Number of poles 1 P

**Compatibility**

Intended for the compatible references Modular devices

**Main electrical features**

Rated operational voltage Ue 415 V

**Voltage**

Max operating voltage 230 V

**Electric current**

Rated current 100 A

**Dimensions**

Length 1000 mm

Pitch 17.8 mm

Fixation distance in module steps 1

**Materials**

Colour stone grey

**Installation, mounting**

Suitable to a device with an auxiliary No

**Connection**

Suitable for product with neutral busbar No

**Equipment**

Number of appliances to build in 57

**Standards**

European directive WEEE not concerned

**Use conditions**

Insulated Yes

KD190B