



Insulated busbar 1P 100A fork 20mm² 57M

Technical properties

Electric current

Rated current 100 A

Architecture

Number of poles 1

Dimensions

Length 1000 mm

Voltage

Rated impulse withstand voltage U_{imp} 4000 V

Connection

Cross-section rigid conductor 20 mm²

Connector/plug type Phase busbar with fork

Capacity

Number of modules 57

KD190B