



KDN180A

Insulated busbar 1P 80A fork 16mm² 12M

Technical properties

Architecture

Number of poles	1 P
Type of pole	1 P

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	415 V
------------------------------	-------

Voltage

Max operating voltage	230 V
-----------------------	-------

Electric current

Rated current	80 A
---------------	------

Dimensions

Length	210 mm
Pitch	17.8 mm

Materials

Colour	stone grey
--------	------------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Connection cross-sect. rigid cable	16mm ²
Suitable for product with neutral busbar	No

Equipment

Number of appliances to build in	12
----------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Insulated	Yes
-----------	-----