



Insulated busbar 1P 80A fork 16mm² 18M

Technical properties

Electric current

Rated current	80 A
---------------	------

Architecture

Number of poles	1
-----------------	---

Dimensions

Length	319 mm
--------	--------

Voltage

Rated impulse withstand voltage U _{imp}	4000 V
--	--------

Rated operational voltage U _e	415 - 415 V
--	-------------

Connection

Cross-section rigid conductor	16 mm ²
-------------------------------	--------------------

Connector/plug type	Phase busbar with fork
---------------------	------------------------

Capacity

Number of modules	18
-------------------	----

KDN180G